

PRODUCT NAME:

GRT™-Reinforced Webbing Adapter ___


WITH MULTI-BELT STABILIZER (MBS)

PART NUMBER


GRT-WAR01


ADJUST MBS FOR DIFFERENT BELT WIDTHS













Feed the Webbing Adapter Lock through the desired two columns webbing on the bottom row of MOLLE as shown.



Feed the GRT™ Reinforced Webbing Adapter tabs into the row of MOLLE above the row the Webbing Adapter Lock is located. Ensure that the GRT™ Reinforced Webbing Adapter snaps are prepared to feed into the Webbing Adapter Lock.



Once the GRT™ Reinforced Webbing Adapter tabs are fed into the top row of MOLLE, pull the adapter down and into the Webbing Adapter Lock. The GRT™ Reinforced Webbing Adapter should snap into the Webbing Adapter Lock indicating that it is secured.

OPEN CAMERA TO VIEW USER INSTRUCTIONS OR VISIT WWW.SSPGEAR.COM/ **END-USER-INSTRUCTIONS**



as shown in the image on the right.